

Garant GRIDLINE

Workbench, mobile, left side cupboard, right side 5 drawers, Beech marine ply worktop, 20×20G, Worktop length: 1250mm**Order data**

Order number	924094 1250
GTIN	4062406101824
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners, single-handed individual drawer release system and 75 kg load capacity.

With 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with **treadless polyurethane tyres**, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads.

Fitted with:

Door height (left) mm: 625

Drawer front height (right): 1

Drawer front height (right) mm: 75, 75, 100, 125, 250

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Worktop length	1250 mm
Material of wheel	Polyurethan

Castor Ø	125 mm
Support cabinet width	1100 mm
Treadless tyres	yes
Number of doors	1
Worktop thickness	25 mm
Push handle	no
Number of drawers	5
Material of worktop	Beech marine ply
Drawer body usable height	625 mm
Fixed wheel Ø	125 mm
Drawer usable area in G	20×20
Drawer usable depth	500 mm
Drawer usable width in G	20
ComfortClose	no
Bumper	no
can be lowered	no
Weight	149.8 kg
Support cabinet depth	700 mm
Worktop depth	750 mm
Height	950 mm
Series	Ready-to-go
Drawer usable width	500 mm
Drawer usable depth in G	20
Individual drawer release system	One-hand
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg

Insert thickness	25 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	mobile workbench

Accessories

Lock plate for GridLine Type KO21	914227 KO21
Drawer with one-handed individual drawer release system Drawer front height 100 mm	927805 100
Slide handle for GridLine Type KO12	914226 KO12
Drawer with one-handed individual drawer release system Drawer front height 250 mm	927805 250
Drawer with one-handed individual drawer release system Drawer front height 75 mm	927805 75
Drawer with one-handed individual drawer release system Drawer front height 200 mm	927805 200