

Garant GRIDLINE

Workbench, mobile, left side cupboard, right side 4 drawers, Bamboo worktop, 20×20G, Worktop length: 1250 mm



Order data

| | |
|--------------|---------------|
| Order number | 924051 1250 |
| GTIN | 4062406101794 |
| Item class | 9GG |

Description

Version:

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners, single-handed individual drawer release system and 75 kg load capacity.

With 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with **treadless polyurethane tyres**, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads.

Fitted with:

Door height (left) mm: 625

Number of height-adjustable shelves (left): 1

Drawer front height (right) mm: 75, 100, 200, 250

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Individual drawer release system: One-hand

Drawer usable area in G: 20×20

Height: 950 mm

Worktop length: 1250 mm

Worktop depth: 750 mm

Worktop thickness: 25 mm

Support cabinet width: 1100 mm

Support cabinet depth: 700 mm

Technical description

| | |
|----------------------------------|-----------------------------------|
| Number of drawers | 4 |
| Worktop depth | 750 mm |
| ComfortClose | no |
| Weight | 135.2 kg |
| Drawer body usable height | 625 mm |
| Support cabinet width | 1100 mm |
| Castor Ø | 125 mm |
| Height | 950 mm |
| Series | Ready-to-go |
| Drawer usable width in G | 20 |
| can be lowered | no |
| Drawer usable width | 500 mm |
| Material of wheel | Polyurethan |
| Worktop thickness | 25 mm |
| Drawer usable area in G | 20×20 |
| Treadless tyres | yes |
| Fixed wheel Ø | 125 mm |
| Material of worktop | Bamboo |
| Bumper | no |
| Support cabinet depth | 700 mm |
| Drawer usable depth | 500 mm |
| Worktop length | 1250 mm |
| Drawer usable depth in G | 20 |
| Number of doors | 1 |
| Push handle | no |
| Individual drawer release system | One-hand |
| Design version | Steel hollow section construction |

| | |
|-------------------------------------------------------------------|----------------------------------------------------------------|
| Material thickness | 1 mm |
| Workbench height | 950 mm |
| Drawer/pull-out shelf load capacity | 75 kg |
| Workbench/desk load capacity - maximum distributed load (on wood) | 400 kg |
| Insert thickness | 25 mm |
| Drawer runner extension (partial/full extension) | 100 % |
| Door opening angle | 180 degrees |
| Cylinder lock | modular lock barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute | 20x20G |
| Type of product | Workbench mobile |

Accessories

| | |
|-------------------------------------------------------------------------------------|-------------|
| Slide handle for GridLine Type KO12 | 914226 KO12 |
| File set Number of tools 6 | 952253 6 |
| Screwdriver set Number of tools 10 | 953521 10 |
| Socket set 1/2 inch Number of tools 32 | 953821 32 |
| Socket set 1/4 inch and 1/2 inch Number of tools 37 | 953828 37 |
| Socket set 1/4 inch and 1/2 inch Number of tools 39 | 953833 39 |
| Pliers set Number of tools 5 | 954295 5 |
| Pliers set Number of tools 5 | 954305 5 |
| Hammer set Number of tools 3 | 954690 3 |
| Marking out and sawing Number of tools 8 | 954895 8 |
| Combination spanner set Number of tools 20 | 952505 20 |
| Lock plate for GridLine Type KO21 | 914227 KO21 |
| Drawer with one-hand individual drawer release system Drawer front height 100 mm | 927805 100 |

| | |
|-------------------------------------------------------------------------------------|--------------|
| Drawer with one-hand individual drawer release system Drawer front height 200 mm | 927805 200 |
| Drawer with one-hand individual drawer release system Drawer front height 250 mm | 927805 250 |
| Drawer with one-hand individual drawer release system Drawer front height 75 mm | 927805 75 |
| easyPick small parts storage bins set Drawer front height / type 75/1 | 950300 75/1 |
| easyPick small parts storage bins set Drawer front height / type 75/2 | 950300 75/2 |
| easyPick small parts storage bins set Drawer front height / type 75/3 | 950300 75/3 |
| Slotted dividers / plain dividers set Drawer front height / type 100/1 | 950320 100/1 |
| Slotted dividers / plain dividers set Drawer front height / type 100/2 | 950320 100/2 |
| Slotted dividers / plain dividers set Drawer front height / type 100/3 | 950320 100/3 |
| Slotted dividers / plain dividers set Drawer front height / type 75/1 | 950320 75/1 |
| Slotted dividers / plain dividers set Drawer front height / type 75/2 | 950320 75/2 |
| Slotted dividers / plain dividers set Drawer front height / type 75/3 | 950320 75/3 |
| Mat for drawers Dimension in G 20X20 | 951830 20X20 |
| Non-slip mats set for drawers, 5 pieces Dimension in G 20X20 | 951885 20X20 |
| Ribbed rubber mat for drawers Dimension in G 20X20 | 951910 20X20 |
| Cleaner and care oil set Type 1 | 926403 1 |
| Workshop set Number of tools 22 | 955071 22 |
| Workshop set Number of tools 26 | 955081 26 |