

Garant GRIDLINE

Workbench, self-propelled with electric drive, left side cupboard, right side 4 drawers, Eluplan worktop, dark, 20×20G, Worktop length: 1250mm



Order data

Order number	925427 1250
GTIN	4062406102111
Item class	9GG

Description

Version:

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer casing 24G and cupboard casing 16G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners, single-handed individual drawer release system and 75 kg load capacity.

Power supply for the drive unit by the integral battery.

Drive unit: Maximum speed **4 km/h**, travel direction forwards and reverse, ground clearance 30 mm, rubber treadless wheels, mechanical emergency release, audible noise energy (drive) 45 dB(A).

With 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with **treadless polyurethane tyres**, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads.

Function:

IPX4: Protected against splashed water from all directions, but without any protection against foreign bodies or touching.

Fitted with:

Door height (left) mm: 625

Number of height-adjustable shelves (left): 1

Drawer front height (right) mm: 75, 100, 200, 250

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

ComfortClose	no
maximum lifting force	400 N
Number of fixed wheels without parking brake	2
Number of castors with parking brake	2
Nominal voltage	24 V
Drawer usable depth in G	20
Series	Ready-to-go
Drawer usable area in G	20×20
Drawer body usable height	625 mm
Worktop depth	750 mm
Treadless tyres	yes
Drawer usable depth	500 mm
Drawer usable width in G	20
Castor Ø	125 mm
Worktop length	1250 mm
Worktop thickness	25 mm
Material of worktop	Eluplan, dark
Support cabinet depth	700 mm
Weight	171 kg
Number of drawers	4
Push handle	yes
Height	950 mm
Rated power	73 W
Support cabinet width	1100 mm
Number of doors	1
Fixed wheel Ø	125 mm
can be lowered	no

Drawer usable width	500 mm
Individual drawer release system	One-hand
Type of rechargeable battery	Lithium-ion
IP Index of Protection	IP X4
Power supply	Rechargeable battery-powered
Power supply	Mains operated
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	25 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	mobile workbench

Accessories

Lock plate for GridLine Type KO21	914227 KO21
Drawer with one-handed individual drawer release system Drawer front height 100 mm	927805 100
Drawer with one-handed individual drawer release system Drawer front height 200 mm	927805 200
Drawer with one-handed individual drawer release system Drawer front height 75 mm	927805 75

Slide handle for GridLine Type KO12	914226 KO12
Drawer with one-handed individual drawer release system Drawer front height 250 mm	927805 250