

Garant GRIDLINE

**Hexagonal workbench, 20×20G, Model: 6****Order data**

Order number	925804 6
GTIN	4062406102135
Item class	9GG

**Description****Version:**

Hexagonal workbench in sturdy steel construction. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Model 6 with **6 drawers**, model 7 with **7 drawers** per unit.

50 mm thick worktop made of beech marine ply. Finished with clear UV varnish.

**Fitted with:**

Drawer front heights, mm: 75, 75, 100, 100, 150, 200

**Supplied with:**

6 drawer casings, 6 intermediate panels, worktop, fastenings.

**Colour:**

Casing body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Number of drawers	6
Drawer body height	800 mm
Drawer usable width	500 mm
Drawer body depth	650 mm

Drawer body width	600 mm
Weight	600 kg
Surface worktop	clear varnished
Drawer usable depth	500 mm
Height	850 mm
ComfortClose	no
Series	vario
Material of worktop	Beech marine ply
Drawer usable area in G	20×20
Drawer usable width in G	20
Drawer usable depth in G	20
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	2000 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Hexagonal workbench

## Accessories

Drawer Drawer front height 150 mm	927800 150
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 100 mm	927800 100

Drawer Drawer front height 200 mm	927800 200
Drawer Drawer front height 75 mm	927800 75