

Garant GRIDLINE

Hexagonal workbench, 20×20G, Model: T3



Order data

Order number	925814 T3
GTIN	4062406102159
Item class	9GG

Description

Version:

Hexagonal workbench in sturdy steel construction. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

50 mm thick worktop made of beech marine ply. Finished with clear UV varnish.

Fitted with:

Drawer front heights, mm: 75, 75, 100

Door heights, mm: 425

Supplied with:

6 drawer casings, 6 intermediate panels, worktop, fastenings.

Colour:

Casing body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Drawer usable area in G: 20×20

Height: 850 mm

Drawer body height: 800 mm

Drawer body width: 600 mm

Drawer body depth: 650 mm

Drawer usable width: 500 mm

Drawer usable depth: 500 mm

Technical description

Drawer body height	800 mm
Drawer body width	600 mm
Drawer usable width	500 mm
Drawer body depth	650 mm
Material of worktop	Beech marine ply
Surface worktop	clear varnished
Drawer usable depth	500 mm
Weight	462 kg
Height	850 mm
Number of drawers	3
ComfortClose	no
Series	vario
Drawer usable area in G	20×20
Drawer usable depth in G	20
Drawer usable width in G	20
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	2000 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Hexagonal workbench

Accessories

Intermediate plate for hexagonal workbench suitable for housing width 600 mm	933522 600
Slide handle for GridLine Type KO12	914226 KO12
File set Number of tools 6	952253 6
Combination spanner set Number of tools 20	952505 20
Screwdriver set Number of tools 10	953521 10
Socket set 1/2 inch Number of tools 32	953821 32
Socket set 1/4 inch and 1/2 inch Number of tools 37	953828 37
Socket set 1/4 inch and 1/2 inch Number of tools 39	953833 39
Pliers set Number of tools 5	954295 5
Pliers set Number of tools 5	954305 5
Hammer set Number of tools 3	954690 3
Marking out and sawing Number of tools 8	954895 8
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 75 mm	927800 75
easyPick small parts storage bins set Drawer front height / type 75/1	950300 75/1
easyPick small parts storage bins set Drawer front height / type 75/2	950300 75/2
easyPick small parts storage bins set Drawer front height / type 75/3	950300 75/3
Slotted dividers / plain dividers set Drawer front height / type 100/1	950320 100/1
Slotted dividers / plain dividers set Drawer front height / type 100/2	950320 100/2
Slotted dividers / plain dividers set Drawer front height / type 100/3	950320 100/3
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1
	950320 75/2

Slotted dividers / plain dividers set Drawer front height /
type 75/2

Slotted dividers / plain dividers set Drawer front height /
type 75/3

950320 75/3

Mat for drawers Dimension in G 20X20

951830 20X20

Non-slip mats set for drawers, 5 pieces Dimension in G
20X20

951885 20X20

Ribbed rubber mat for drawers Dimension in G 20X20

951910 20X20

Comfort Close drawer closure damping system Load
capacity of the drawer 75 kg

950180 75

Workshop set Number of tools 22

955071 22

Workshop set Number of tools 26

955081 26