

Weidmüller **Cable cutter, with 2-component grips VDE insulated, overall length: 245mm****Order data**

Order number	730250 245
GTIN	4032248945528
Item class	73H

Description**Version:**

Handles with **insulation up to 1000 Volts to DIN EN 60900 / VDE 0682-201**.

Head with sickle-shaped blades. Handles with plastic grips. Cuts smoothly and cleanly without crushing.

Application:

For cutting copper and aluminium cables.

Material:

Special tool steel, drop-forged.

Technical description

Cutting capacity	95 mm ²
overall length	245 mm
Cutting capacity up to Ø	22 mm
Manufacturer's designation	KT22
Standard	DIN EN IEC 60900 / VDE 0682-201
Handle	Plastic covering
Operation	mechanical, single-handed
Material	Special tool steel, drop-forged
Surface	bright finish
with return spring	no

Type of product

Scissors