

Garant
HSS parting-off tool, neutral, Blade height h₅ / groove width w: 19/3,1 mm


Order data

| | |
|--------------|---------------|
| Order number | 273560 19/3,1 |
| GTIN | 4045197719171 |
| Item class | 21U |

Description

Suitable for:

Toolholder No. 273984 – 273994 or No. 319132; 319133 (VDI toolholder).

Attention:

Please order the assembly key No. 279940 separately.

Technical description

| | |
|------------------------------------|------------------|
| Blade height h ₅ | 19 mm |
| Groove width w | 3.1 mm |
| for maximum workpiece Ø | 40 mm |
| max. groove depth t _{max} | 21 mm |
| Overall length L | 86 mm |
| Tool material | HSS |
| Application type | neutral |
| Through-coolant | no |
| axial grooving possible | no |
| Type of product | Parting-off tool |