

Garant**Insert for the revolving lathe centre, Type: 4****Order data**

| | |
|--------------|---------------|
| Order number | 320625 4 |
| GTIN | 4045197719713 |
| Item class | 31Z |

Description**Version:**

- **High flexibility due to range of geometries on the same carrier tool.**
- **Fully hardened and ground.**
- **Quick and efficient exchange of worn tools.**

Suitable for :

Lathe centre No. 320615, No. 320617, No. 320659 size 2, No. 321265 size 3, No. 321335 size 2.
suitable for colour code: K12

External \varnothing D: 28 mm

small tip \varnothing D₁: 13 mm

Shank \varnothing d: 12 mm

Reach L₁: 23 mm

Point angle: 60 °

Width across flats: 17 mm

Technical description

| | |
|--|-------|
| small tip \varnothing D ₁ | 13 mm |
| Reach L ₁ | 23 mm |

| | |
|--------------------------|----------------|
| Shank Ø d | 12 mm |
| External Ø D | 28 mm |
| Point angle | 60 ° |
| Width across flats | 17 mm |
| suitable for colour code | K12 |
| Type of product | Centring drill |