

**Garant****Insert for the revolving lathe centre, Type: 5****Order data**

Order number	320625 5
GTIN	4045197719720
Item class	31Z

**Description****Version:**

- **High flexibility due to range of geometries on the same carrier tool.**
- **Fully hardened and ground.**
- **Quick and efficient exchange of worn tools.**

**Suitable for :**

Lathe centre No. 320615, No. 320617, No. 320659 size 2, No. 321265 size 3, No. 321335 size 2.  
suitable for colour code: K12

External  $\varnothing$  D: 20 mm

small tip  $\varnothing$  D<sub>1</sub>: 10 mm

Shank  $\varnothing$  d: 12 mm

Reach L<sub>1</sub>: 17 mm

Point angle: 60 °

Width across flats: 22 mm

**Technical description**

Shank $\varnothing$ d	12 mm
Reach L <sub>1</sub>	17 mm

small tip $\varnothing D_1$	10 mm
External $\varnothing D$	20 mm
Point angle	60°
Width across flats	22 mm
suitable for colour code	K12
Type of product	Centring drill