



Climate measuring instrument Air flow kit, Type: HD



Order data

Order number	474162 HD
GTIN	4029547019364
Item class	47B

Description

Version:

Testo 440 climatic measuring instrument for measuring the **flow speed and volumetric flow in air ducts (m/s, m³/h)**. Hot wire measurement probe (sensor head Ø 9 mm) for small airflows up to 30 m/s. Supplied with a temperature sensor.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Testo 440 climatic measuring instrument No. 474141 size 440, 3× mignon batteries type AA, USB cable, case No. 474161 size K and calibration certificate. Hot wire probe No. 474152 size FR

Technical description

Measuring range	0 - 30 m/s
Error limit (m/s + % of measured value)	±0.03 + 4 % (0 to 20 m/s) ±0.5 + 5 % (20.01 to 30 m/s)
Operating temperature	-20 - 70 °C
IP Index of Protection	IP 54

Power supply	Battery-powered
Battery type	Mignon, AA
Number of batteries contained	3
Interface	USB interface
Interface	Bluetooth interface
Calibration	Price on request
Type of product	Climate measuring instrument

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------