

**Garant**
**Insert for the revolving lathe centre, Type: 1**

**Order data**

Order number	320625 1
GTIN	4045197719089
Item class	31Z

**Description**
**Version:**

- **High flexibility due to range of geometries on the same carrier tool.**
- **Fully hardened and ground.**
- **Quick and efficient exchange of worn tools.**

**Suitable for :**

Lathe centre No. 320615, No. 320617, No. 320659 size 2, No. 321265 size 3, No. 321335 size 2.  
suitable for colour code: K12

External  $\varnothing$  D: 14 mm

small tip  $\varnothing$  D<sub>1</sub>: 4 mm

Shank  $\varnothing$  d: 12 mm

Reach L<sub>1</sub>: 32 mm

Point angle: 60 °

Point angle: 30 °

**Technical description**

Shank $\varnothing$ d	12 mm
small tip $\varnothing$ D <sub>1</sub>	4 mm

Reach L <sub>1</sub>	32 mm
External Ø D	14 mm
Point angle	60 °
Point angle	30 °
Width across flats	12 mm
suitable for colour code	K12
Type of product	Centring drill