



## ER clamping nut with radial run-out adjustment, for ER: 32



### Order data

Order number	309619 32
GTIN	2050002004030
Item class	33E

### Description

**Version:**

Thread and taper ground in a single setup for highest concentricity.  
6 screws allow the radial run-out to be reduced to zero. **With slots.**

**Suitable for:**

All standard ER collet chucks.

Ideally suitable for lathes, both for stationary and driven tools.

**Optional extras:**

ER clamping wrench, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

**Note:**

Collet chuck and clamping nut are balanced separately!  
Up to 6000 rpm.

### Technical description

Thread	M40×1.5
for ER	32 mm

External Ø D	63 mm
Overall length L	23 mm
Standard	DIN 6499 D
Type of product	Clamping nut