

Garant
Synchro tool head for ER25, Tap shank \varnothing d₂: 9mm

Order data

Order number	338185 9
GTIN	4062406103613
Item class	31P

Description
Version:

- **Tapping and thread forming on machines with synchronised spindles.**
- **Minimum Length Adjustment: +0.5mm / -0.2 mm.**
- **Compensation for synchronisation errors, hence better thread quality and clear increase in tool life.**
- **For collet chucks and driven tools to ISO 15488 (DIN 6499).**
- **Suitable for left-hand and right-hand threads.**

Version of the advertising text:

- **Minimum Length Adjustment: +0.5mm / -0.2 mm.**
- **Compensation for synchronisation errors, hence better thread quality and clear increase in tool life.**

Suitable for:

ER synchro collet No. 338180.

Technical description

Overhang L ₁	40 mm
Shank square	7 mm
for tap shank \varnothing d ₂ DIN 374/376	M12
for tap shank \varnothing d ₂ DIN 371	M9
\varnothing D ₂	19 mm
Through-coolant	yes, with max. 50 bar

Type of product

Tapping adapter