

**Garant**
**Synchro tool head for ER25, Tap shank  $\varnothing$  d2: 10mm**

**Order data**

Order number	338185 10
GTIN	4062406103620
Item class	31P

**Description**
**Version:**

- Tapping and thread forming on machines with synchronised spindles.
- Minimum Length Adjustment: +0.5mm / -0.2 mm.
- Compensation for synchronisation errors, hence better thread quality and clear increase in tool life.
- For collet chucks and driven tools to ISO 15488 (DIN 6499).
- Suitable for left-hand and right-hand threads.

**Version of the advertising text:**

- Minimum Length Adjustment: +0.5mm / -0.2 mm.
- Compensation for synchronisation errors, hence better thread quality and clear increase in tool life.

**Suitable for:**

ER synchro collet No. 338180.

**Technical description**

Overhang $L_1$	41 mm
Shank square	8 mm
$\varnothing$ $D_2$	19 mm
Through-coolant	yes, with max. 50 bar
Type of product	Tapping adapter

