

Garant
Synchro tool head for ER32, Tap shank \varnothing d₂: 6mm

Order data

Order number	338186 6
GTIN	4062406103637
Item class	31P

Description
Version:

- Tapping and thread forming on machines with synchronised spindles.
- Minimum Length Adjustment: +0.5mm / -0.2 mm.
- Compensation for synchronisation errors, hence better thread quality and clear increase in tool life.
- For collet chucks and driven tools to ISO 15488 (DIN 6499).
- Suitable for left-hand and right-hand threads.

Version of the advertising text:

- Minimum Length Adjustment: +0.5mm / -0.2 mm.
- Compensation for synchronisation errors, hence better thread quality and clear increase in tool life.

Suitable for:

ER synchro collet No. 338180.

Technical description

Shank square	4.9 mm
Overhang L ₁	8 mm
for tap shank \varnothing d ₂ DIN 374/376	M8
for tap shank \varnothing d ₂ DIN 371	M5-6
\varnothing D ₂	25 mm
Through-coolant	yes, with max. 50 bar

Type of product

Tapping adapter