

Garant**Synchro collet, for ER collets: 32****Order data**

Order number	338180 32
GTIN	4062406103729
Item class	31P

Description**Version:**

- Tapping and thread forming on machines with synchronised spindles.
- Minimum Length Adjustment: +0.5mm / -0.2 mm.
- Compensation for synchronisation errors, hence better thread quality and clear increase in tool life.
- For collet chucks and driven tools to ISO 15488 (DIN 6499).
- Suitable for left-hand and right-hand threads.

Version of the advertising text:

- Tapping and thread forming on machines with synchronised spindles.
- Minimum Length Adjustment: +0.5mm / -0.2 mm.
- Compensation for synchronisation errors, hence better thread quality and clear increase in tool life.
- For collet chucks and driven tools to ISO 15488 (DIN 6499).
- Suitable for left-hand and right-hand threads.

Suitable for:

ER collet chuck.

Technical description

Through-coolant	yes, with max. 50 bar
Type of product	Collet holder

