




ER collet, ER 25, Nominal clamping \varnothing d: 1/4mm



Order data

Order number	308960 1/4
GTIN	4062406103965
Item class	32Z

Description

Version:

Through hardened and ground. Polished.

Note:

The **collet clamping \varnothing range is always up to 1 mm less than nominal**, e.g. \varnothing 10 – 9 mm, **except for \varnothing 1, 1.5 and 2 (where it is only 0.5 mm)**.

Collets ER16, ER25 and ER32 without a seal also available in inch sizes via the eShop.

Technical description

Adapter	ER 25
Standard	ISO 15488-B
Concentricity	$\leq 10 \mu\text{m}$
Type	430 E
External \varnothing D	26 mm
Overall length L	34 mm
Type of product	Collet

