

SWISS TOOLS

## Boring bar shank vibration-damped, PSC, Shank $\emptyset$ / $\emptyset$ D – A dimension: 63/40-225 mm



### Order data

Order number	320408 63/40-225
GTIN	2050001772657
Item class	36D

### Description

#### Version:

- For efficient turning.
- For left-hand and right-hand turning.

#### Application:

For mounting exchangeable cutting heads.

#### Note:

For suitable interchangeable heads see No. 264826 – 264827.

Through-coolant: yes

### Technical description

Overhang dimension A	225 mm
Shank $\emptyset$	63 mm
$\emptyset$ D	40 mm
Adapter	PSC
Arbor standard	ISO 26623-1
Through-coolant	yes
Type of product	Boring bar base body

