

**Draw-in collet, round, to DIN 6341, 355 E, Clamping Ø: 15mm****Order data**

Order number	329705 15
GTIN	4062406104634
Item class	32B

Description**Version:**

Collets, **round profile in 1 mm increments. Please specify required clamping Ø with order.**

Saw thread

Standard:

DIN 6341

Accuracy:

Concentricity tolerances: D = 1 to 10 mm = 0.02 mm D = 10 to 30 mm = 0.03 mm D = 30 to 60 mm = 0.04 mm

Note:

Other diameters and profiles (e.g. square or hexagon) **on request!**

Technical description

F	20 mm
Overall length L	123 mm
K	28 mm
Angle α	17.5 degrees
Buttress thread G	S20x2 mm
Standard	DIN 6341
Type	355 E
Type of product	Collet

