



Draw-in collet, round, to DIN 6341, 386 E, Clamping Ø: 17mm



Order data

Order number	329755 17
GTIN	4062406104818
Item class	32B

Description

Version:

Collets, **round profile in 1 mm increments. Please specify required clamping Ø with order.**
Trapezoidal thread

Standard:

DIN 6341

Accuracy:

Concentricity tolerances: D = 1 to 10 mm = 0.02 mm D = 10 to 30 mm = 0.03 mm D = 30 to 60 mm = 0.04 mm

Note:

Other diameters and profiles (e.g. square or hexagon) **on request!**

Technical description

Overall length L	115 mm
F	32 mm
Trapezoidal thread G	Tr32×1.5 mm
Angle α	20 degrees
K	45 mm
Standard	DIN 6341
Type	386 E
Type of product	Collet

