

## Flat magnet 2-part set with threaded stud, Neodymium, Ø: 88mm



### Order data

Order number	085926 88
GTIN	5012095608431
Item class	08Q

### Description

#### Version:

- **Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.**
- **Corrosion resistance and surface protection due to the rubberised surface.**
- **Rubberisation increases the lateral holding forces.**
- **Neodymium magnetic core.**

#### Application:

On painted surfaces, will not scratch or slip.

### Technical description

Material of the surface	rubberised
Height with thread	23.5 mm
Height	8.5 mm
Nominal clamping force	420 N
Ø	88 mm
Thread	M8 mm
Material of the magnet core	Neodymium
Type of product	Flat gripper magnet

