

## Flat magnet 2-part set with threaded stud, Neodymium, Ø: 43mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 085926 43     |
| GTIN         | 5012095608394 |
| Item class   | 08Q           |

### Description

#### Version:

- **Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.**
- **Corrosion resistance and surface protection due to the rubberised surface.**
- **Rubberisation increases the lateral holding forces.**
- **Neodymium magnetic core.**

#### Application:

On painted surfaces, will not scratch or slip.

### Technical description

|                             |                     |
|-----------------------------|---------------------|
| Thread                      | M6 mm               |
| Ø                           | 43 mm               |
| Material of the surface     | rubberised          |
| Nominal clamping force      | 85 N                |
| Height with thread          | 21 mm               |
| Height                      | 6 mm                |
| Material of the magnet core | Neodymium           |
| Type of product             | Flat gripper magnet |

