

Flat magnet 2-part set with threaded socket, Neodymium, Ø: 66mm



Order data

Order number	085927 66
GTIN	5012095608424
Item class	08Q

Description

Version:

- **Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.**
- **Corrosion resistance and surface protection due to the rubberised surface.**
- **Rubberisation increases the lateral holding forces.**
- **Neodymium magnetic core.**

Application:

On painted surfaces, will not scratch or slip.

Note:

Screw-in hooks with external thread under No. 085921.

Technical description

Ø	66 mm
Height with thread	15 mm
Material of the surface	rubberised
Threaded socket	yes
Height	8.5 mm
Thread	M5 mm
Nominal clamping force	180 N

Material of the magnet core	Neodymium
Type of product	Flat gripper magnet

Accessories

Screw-in hook set with external thread 10 pieces Thread M5	085921 M5
--	-----------