

**Flat magnet with bore, Neodymium, Ø: 32mm****Order data**

Order number	085932 32
GTIN	5012095608509
Item class	08Q

**Description****Version:**

- **Temperature-resistant up to maximum 80 °C.**
- **Galvanised surface, magnetic core made of neodymium.**
- **Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.**

**Application:**

For clamping, assembling, incorporation by screw fastening.

**Technical description**

Ø	32 mm
maximum temperature resistance	80 °C
Nominal clamping force	310 N
Height	7 mm
Bore Ø	5.5 mm
Material of the magnet core	Neodymium
Type of product	Flat gripper magnet

