

## Flat magnet 2-part set with threaded stud, Neodymium, Ø: 22mm



### Order data

Order number	085926 22
GTIN	5012095608370
Item class	08Q

### Description

#### Version:

- **Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.**
- **Corrosion resistance and surface protection due to the rubberised surface.**
- **Rubberisation increases the lateral holding forces.**
- **Neodymium magnetic core.**

#### Application:

On painted surfaces, will not scratch or slip.

### Technical description

Height	6 mm
Nominal clamping force	50 N
Thread	M4 mm
Height with thread	12.5 mm
Material of the surface	rubberised
Ø	22 mm
Material of the magnet core	Neodymium
Type of product	Flat gripper magnet

