

**Boring bar blank Form A, BT 50, A dimension: 315mm****Order data**

Order number	302891 315
GTIN	4062406105051
Item class	32A

Description**Version:**

Taper with collar, hardened and ground. Soft shank for further machining.

Optional extras:

Pull studs (PS) No. 308760 – 308802.

Technical description

External \varnothing D	97 mm
Overhang dimension A	315 mm
Clamping \varnothing D ₁	97 mm
Adapter	BT 50
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	A
Type of product	Boring bar blank

Accessories

Pull stud 45°sealed suitable for steep tapers 50	308760 50
--	-----------

Pull stud 90°sealed suitable for steep tapers 50	308795 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50