



Boring bar blank, HSK-A 100, A dimension: 250mm



Order data

| | |
|--------------|---------------|
| Order number | 307027 250 |
| GTIN | 4062406105075 |
| Item class | 32A |

Description

Version:

- Taper and collar hardened and ground.
- Shank soft for further machining.

Application:

For making special tools.

Material:

16MnCr5.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Technical description

| | |
|---------------------------------------|------------------|
| External \varnothing D | 97 mm |
| Overhang dimension A | 250 mm |
| Clamping \varnothing D ₁ | 97 mm |
| Adapter | HSK-A 100 |
| Arbor standard | ISO 12164-1 |
| Arbor standard | DIN 69893 |
| Shape | A |
| Type of product | Boring bar blank |

