



Boring bar blank, HSK-A 63, A dimension: 160mm



Order data

| | |
|--------------|---------------|
| Order number | 307025 160 |
| GTIN | 4062406105068 |
| Item class | 32A |

Description

Version:

- Taper and collar hardened and ground.
- Shank soft for further machining.

Application:

For making special tools.

Material:

16MnCr5.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Technical description

| | |
|---------------------------------------|------------------|
| Overhang dimension A | 160 mm |
| External \varnothing D | 63 mm |
| Clamping \varnothing D ₁ | 63 mm |
| Adapter | HSK-A 63 |
| Arbor standard | ISO 12164-1 |
| Arbor standard | DIN 69893 |
| Shape | A |
| Type of product | Boring bar blank |

Accessories

HSK coolant tube for HSK 63

309880 63