

**Garant****Toolholder for indexable drills, HSK-A 63, for shank Ø D1: 40mm****Order data**

Order number	307005 40
GTIN	4062406105266
Item class	31A

**Description****Version:**

Position of the threaded pin for countersinking in the indexable drill offset by 0.4 mm.

**Tightening the lock screw clamps the indexable drill collar against the front face of the holder. In addition the contact face Ø is larger** than for conventional toolholders.

**Application:**

**For mounting all standard indexable drills to DIN 6595, Part 1.**

**Suitable for:**

All indexable drills with parallel shank to DIN 6595, Part 1.

**Optional extras:**

Coolant tube No. 309880, socket wrench No. 309890, spare screws No. 309907 and 309908.

**Technical description**

Overhang dimension A	105 mm
for shank Ø D <sub>1</sub>	40 mm
External Ø D	60 mm
Adapter	HSK-A 63
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Machining strategy	HPC
Type of product	Indexable drill head adapter

---

## Accessories

HSK coolant tube for HSK 63	309880 63
-----------------------------	-----------