

Flat magnet 2-part set with threaded socket, Neodymium, Ø: 22mm



Order data

Order number	085927 22
GTIN	5012095608387
Item class	08Q

Description

Version:

- **Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.**
- **Corrosion resistance and surface protection due to the rubberised surface.**
- **Rubberisation increases the lateral holding forces.**
- **Neodymium magnetic core.**

Application:

On painted surfaces, will not scratch or slip.

Note:

Screw-in hooks with external thread under No. 085921.

Technical description

Threaded socket	yes
Thread	M4 mm
Height with thread	11 mm
Height	6 mm
Material of the surface	rubberised
Ø	22 mm
Nominal clamping force	50 N

Material of the magnet core	Neodymium
Type of product	Flat gripper magnet

Accessories

Screw-in hook set with external thread10 pieces Thread M4	085921 M4
---	-----------