

**HOLEX®**
**Extendable telescopic precision ratchet, 1/2 inch, Type:**

**Order data**

Order number	640295
GTIN	4045197720214
Item class	62A

**Description**
**Version:**

Material selection and special forging method guarantee optimal functioning and long life. Fixing is performed by the locking ring. With reversing lever for right-hand and left-hand threads.

**Maximum permissible torque 600 Nm.**

Extendable from 290 – 430 mm length in 6 stages. **With lockable swivel head and ejector.**

**Standard:**

Außenvierkante nach **DIN 3120-A 12,5** mit federnder Kugel.

**Suitable for :**

Manual use.  
 Square drive: 1/2 inch  
 No. of teeth: 72

**Technical description**

Square drive	1/2 inch
overall length	290 - 430 mm
No. of teeth	72
stepless pull-out	no