



Base body 6371G-50-500-040 MT shank, with through-coolant, 1.5×D, Type: 36



Order data

Order number	232271 36
GTIN	4062406105846
Item class	22G

Description

Version:

With internal cooling.

Straight fluted.

Note:

Further sizes available on request.

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Through-coolant: yes

Number of cutting edges Z: 2

Dia. range D_c : 36 - 47 mm

Reach L_1 : 70.5 mm

Morse taper MT size: 4

Clamping screws: 232990 TX20

Technical description

Reach L_1	70.5 mm
Clamping screws	232990 TX20
Dia. range D_c	36 - 47 mm
Morse taper MT size	4
Number of cutting edges Z	2
Version	1.5×D
Shank	Morse taper

Through-coolant	yes
Type of product	Indexable drill