



Base body MT shank, with through-coolant, 5×D, Type: 13



Order data

| | |
|--------------|---------------|
| Order number | 232273 13 |
| GTIN | 4062406105938 |
| Item class | 22G |

Description

Version:

With internal cooling.

Note:

Further sizes available on request.

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Through-coolant: yes

Number of cutting edges Z: 2

Dia. range D_c: 13 - 17.5 mm

Reach L₁: 63.5 mm

Morse taper MT size: 2

Clamping screws: 232990 TX8

Technical description

| | |
|---------------------------|-----------------|
| Reach L ₁ | 63.5 mm |
| Morse taper MT size | 2 |
| Clamping screws | 232990 TX8 |
| Dia. range D _c | 13 - 17.5 mm |
| Number of cutting edges Z | 2 |
| Version | 5×D |
| Shank | Morse taper |
| Through-coolant | yes |
| Type of product | Indexable drill |

