



## Base body MT shank, with through-coolant, 3×D, Type: 48



### Order data

|              |               |
|--------------|---------------|
| Order number | 232272 48     |
| GTIN         | 4062406105914 |
| Item class   | 22G           |

### Description

#### Version:

With internal cooling.

#### Straight fluted.

#### Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Through-coolant: yes

Number of cutting edges Z: 2

Dia. range  $D_c$ : 48 - 65 mm

Reach  $L_1$ : 130.1 mm

Morse taper MT size: 5

Clamping screws: 232990 TX20

### Technical description

|                           |             |
|---------------------------|-------------|
| Clamping screws           | 232990 TX20 |
| Dia. range $D_c$          | 48 - 65 mm  |
| Morse taper MT size       | 5           |
| Reach $L_1$               | 130.1 mm    |
| Number of cutting edges Z | 2           |
| Version                   | 3×D         |
| Shank                     | Morse taper |
| Through-coolant           | yes         |

Type of product

Indexable drill