



Base body MT shank, with through-coolant, 12×D, Type: 25



Order data

Order number	232275 25
GTIN	4062406106072
Item class	22G

Description

Version:

With internal cooling.

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Reduce feed rates f by 10% and v_c values by 30%.

Through-coolant: yes

Number of cutting edges Z : 2

Dia. range D_c : 25 - 35 mm

Reach L_1 : 300 mm

Morse taper MT size: 4

Clamping screws: 232990 TX15

Technical description

Dia. range D_c	25 - 35 mm
Clamping screws	232990 TX15
Morse taper MT size	4
Reach L_1	300 mm
Number of cutting edges Z	2
Version	12×D
Shank	Morse taper
Through-coolant	yes
Type of product	Indexable drill

