



Base body MT shank, with through-coolant, 8xD, Type: 13



Order data

Order number	232274 13
GTIN	4062406105990
Item class	22G

Description

Version:

With internal cooling.

Note:

Further sizes available on request.

Reduce feed rates f by 5% and v_c values by 10%.

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Through-coolant: yes

Number of cutting edges Z : 2

Dia. range D_c : 13 - 17.5 mm

Reach L_1 : 114.3 mm

Morse taper MT size: 2

Clamping screws: 232990 TX8

Technical description

Dia. range D_c	13 - 17.5 mm
Clamping screws	232990 TX8
Reach L_1	114.3 mm
Morse taper MT size	2
Number of cutting edges Z	2
Version	8xD
Shank	Morse taper
Through-coolant	yes

Type of product

Indexable drill