



Base body MT shank, with through-coolant, 3×D, Type: 25



Order data

Order number	232272 25
GTIN	4062406105891
Item class	22G

Description

Version:

With internal cooling.

Straight fluted.

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Through-coolant: yes

Number of cutting edges Z: 2

Dia. range D_c : 25 - 35 mm

Reach L_1 : 85.7 mm

Morse taper MT size: 4

Clamping screws: 232990 TX15

Technical description

Clamping screws	232990 TX15
Reach L_1	85.7 mm
Morse taper MT size	4
Dia. range D_c	25 - 35 mm
Number of cutting edges Z	2
Version	3×D
Shank	Morse taper
Through-coolant	yes

Type of product

Indexable drill