



Base body MT shank, with through-coolant, 12×D, Type: 18



Order data

Order number	232275 18
GTIN	4062406106065
Item class	22G

Description

Version:

With internal cooling.

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Reduce feed rates f by 10% and v_c values by 30%.

Through-coolant: yes

Number of cutting edges Z : 2

Dia. range D_c : 18 - 24 mm

Reach L_1 : 288 mm

Morse taper MT size: 3

Clamping screws: 232990 TX9

Technical description

Clamping screws	232990 TX9
Dia. range D_c	18 - 24 mm
Reach L_1	288 mm
Morse taper MT size	3
Number of cutting edges Z	2
Version	12×D
Shank	Morse taper
Through-coolant	yes
Type of product	Indexable drill

