



Base body MT shank, with through-coolant, 12×D, Type: 12



Order data

Order number	232275 12
GTIN	4062406106041
Item class	22G

Description

Version:

With internal cooling.

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Reduce feed rates f by 10% and v_c values by 30%.

Through-coolant: yes

Number of cutting edges Z : 2

Dia. range D_c : 12 - 12.5 mm

Reach L_1 : 144 mm

Morse taper MT size: 2

Clamping screws: 232990 TX7

Technical description

Clamping screws	232990 TX7
Dia. range D_c	12 - 12.5 mm
Reach L_1	144 mm
Morse taper MT size	2
Number of cutting edges Z	2
Version	12×D
Shank	Morse taper
Through-coolant	yes
Type of product	Indexable drill

