



Base body MT shank, with through-coolant, 3×D, Type: 36



Order data

Order number	232272 36
GTIN	4062406105907
Item class	22G

Description

Version:

With internal cooling.

Straight fluted.

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Through-coolant: yes

Number of cutting edges Z: 2

Dia. range D_c : 36 - 47 mm

Reach L_1 : 120.6 mm

Morse taper MT size: 4

Clamping screws: 232990 TX20

Technical description

Dia. range D_c	36 - 47 mm
Reach L_1	120.6 mm
Clamping screws	232990 TX20
Morse taper MT size	4
Number of cutting edges Z	2
Version	3×D
Shank	Morse taper
Through-coolant	yes

Type of product

Indexable drill