



Base body MT shank, with through-coolant, 8xD, Type: 12



Order data

Order number	232274 12
GTIN	4062406105983
Item class	22G

Description

Version:

With internal cooling.

Note:

Further sizes available on request.

Reduce feed rates f by 5% and v_c values by 10%.

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Through-coolant: yes

Number of cutting edges Z: 2

Dia. range D_c : 12 - 12.5 mm

Reach L_1 : 111.1 mm

Morse taper MT size: 2

Clamping screws: 232990 TX7

Technical description

Dia. range D_c	12 - 12.5 mm
Reach L_1	111.1 mm
Morse taper MT size	2
Clamping screws	232990 TX7
Number of cutting edges Z	2
Version	8xD
Shank	Morse taper
Through-coolant	yes

Type of product

Indexable drill