

Garant GRIDLINE

Vario workbench with drawer casing 24G, with electric height adjustment, Bamboo worktop, 20×20G, Worktop length: 1000/DEmm**Order data**

Order number	923291 1000/DE
GTIN	4062406103224
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. With 1 pair of stabilising plates for stiffening. Stepless electric drive for height adjustment. Height adjustment by pushbutton. Connecting cable with German Schuko plug. Power supply 250 V / 50 Hz with maximum 340 W. **100% full extension drawers** with differential runners and 75 kg load capacity. Drawer casing 24G can be locked centrally with cylinder lock.

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

Fitted with:

Drawer front height, mm: 75#150

Supplied with:

2 × support legs with electric height adjustment, 1 × pair of stabilising plates, drawer cabinet, worktop.

Optional extras:

Additional accessories such as side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied as components, not assembled. The position of the manual pushbutton can be freely selected. When benches are installed in a row, it is essential that additional side plates No. 927220 are fitted.

Technical description

Drawer body depth	650 mm
Drawer usable area in G	20×20
maximum load capacity	400 kg
ComfortClose	no
Drawer usable width in G	20
Number of drawers	2
Supply voltage	250 V
Series	vario
Drawer usable depth in G	20
Drawer usable depth	500 mm
Drawer body width	600 mm
Electronic locking system can be retrofitted	yes
Worktop length	1000 mm
Worktop depth	750 mm
Drawer usable width	500 mm
Height adjustment range	850 - 1050 mm
Lifting speed	9 mm/s
Drawer body height	300 mm
Drawer body usable height	225 mm
Weight	74 kg
Worktop thickness	50 mm
IP Index of Protection	IP 20
Power supply	Rechargeable battery-powered

Power supply	Mains operated
Nominal voltage	250 V
Plug type, input	F
Design version	Steel hollow section construction
Material thickness	1 mm
Height adjustment workstation	850-1050 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Type of height adjustment	electrical
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench

Accessories

Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 150 mm	927800 150
Drawer Drawer front height 75 mm	927800 75