

Garant GRIDLINE

**Vario workbench with drawer casing 24G, with electric height adjustment, Beech marine ply worktop, 20×20G, Worktop length: 2000/DEmm****Order data**

Order number	923294 2000/DE
GTIN	4062406103279
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. With 1 pair of stabilising plates for stiffening. Stepless electric drive for height adjustment. Height adjustment by pushbutton. Connecting cable with German Schuko plug. Power supply 250 V / 50 Hz with maximum 340 W. **100% full extension drawers** with differential runners and 75 kg load capacity. Drawer casing 24G can be locked centrally with cylinder lock.

**Function:**

IP20: Protected against penetration by foreign bodies with  $\varnothing < 12$  mm, however touching should be avoided, and offers no protection against water.

**Fitted with:**

Drawer front height, mm: 75#150

**Supplied with:**

2 × support legs with electric height adjustment, 1 × pair of stabilising plates, drawer cabinet, worktop.

**Optional extras:**

Additional accessories such as side panels, etc. can be found under GridLine individual components in Group 92.

**Colour:**

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Supplied as components, not assembled. The position of the manual pushbutton can be freely selected. When benches are installed in a row, it is essential that additional side plates No. 927220 are fitted.

## Technical description

Drawer usable area in G	20×20
Series	vario
Drawer usable depth	500 mm
Drawer body width	600 mm
Height adjustment range	850 - 1050 mm
maximum load capacity	400 kg
Supply voltage	250 V
Lifting speed	9 mm/s
Number of drawers	2
ComfortClose	no
Worktop thickness	50 mm
Drawer usable width	500 mm
Worktop length	2000 mm
Drawer usable depth in G	20
Drawer usable width in G	20
Drawer body depth	650 mm
Drawer body height	300 mm
Weight	104 kg
Electronic locking system can be retrofitted	yes
Worktop depth	750 mm
Drawer body usable height	225 mm
IP Index of Protection	IP 20
Power supply	Rechargeable battery-powered
Power supply	Mains operated
Nominal voltage	250 V

Plug type, input	F
Design version	Steel hollow section construction
Material thickness	1 mm
Height adjustment workstation	850-1050 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Type of height adjustment	electrical
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench

## Accessories

Drawer Drawer front height 150 mm	927800 150
Non-slip mats set for drawers,5 pieces Dimension in G 20X20	951885 20X20
Screwdriver set Number of tools 10	953521 10
Slotted dividers / plain dividers set Drawer front height / type 75/3	950320 75/3
Lock plate for GridLine Type KO21	914227 KO21
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1
Drawer Drawer front height 75 mm	927800 75
Slotted dividers / plain dividers set Drawer front height / type 150/5	950320 150/5

Slotted dividers / plain dividers set Drawer front height / type 75/2	950320 75/2
Mat for drawers Dimension in G 20X20	951830 20X20
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
easyPick small parts storage bins set Drawer front height / type 75/3	950300 75/3
Slotted dividers / plain dividers set Drawer front height / type 150/4	950320 150/4
easyPick small parts storage bins set Drawer front height / type 75/1	950300 75/1
Pliers set Number of tools 5	954305 5
easyPick small parts storage bins set Drawer front height / type 75/2	950300 75/2