

Garant GRIDLINE

Vario workbench with drawer casing 24G, with electric height adjustment, Eluplan worktop, dark, 20×20G, Worktop length: 2000/DEmm**Order data**

Order number	923297 2000/DE
GTIN	4062406103309
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. With 1 pair of stabilising plates for stiffening. Stepless electric drive for height adjustment. Height adjustment by pushbutton. Connecting cable with German Schuko plug. Power supply 250 V / 50 Hz with maximum 340 W. **100% full extension drawers** with differential runners and 75 kg load capacity. Drawer casing 24G can be locked centrally with cylinder lock.

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

Fitted with:

Drawer front height, mm: 75#150

Supplied with:

2 × support legs with electric height adjustment, 1 × pair of stabilising plates, drawer cabinet, worktop.

Optional extras:

Additional accessories such as side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied as components, not assembled. The position of the manual pushbutton can be freely selected. When benches are installed in a row, it is essential that additional side plates No. 927220 are fitted.

Technical description

Drawer usable area in G	20×20
Drawer body usable height	225 mm
Weight	104 kg
Number of drawers	2
Worktop depth	750 mm
Drawer usable width in G	20
Drawer usable width	500 mm
Series	vario
Drawer body height	300 mm
Worktop thickness	50 mm
Drawer body width	600 mm
Worktop length	2000 mm
Height adjustment range	850 - 1050 mm
Drawer usable depth	500 mm
Electronic locking system can be retrofitted	yes
Supply voltage	250 V
maximum load capacity	400 kg
ComfortClose	no
Drawer usable depth in G	20
Drawer body depth	650 mm
Lifting speed	9 mm/s
IP Index of Protection	IP 20
Power supply	Rechargeable battery-powered
Power supply	Mains operated
Nominal voltage	250 V

Plug type, input	F
Design version	Steel hollow section construction
Material thickness	1 mm
Height adjustment workstation	850-1050 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Type of height adjustment	electrical
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench