

**Garant****Arbor for screw-in milling cutters with thread tapered form, HSK-A 63, Thread M × Length L1: M8X25****Order data**

Order number	307044 M8X25
GTIN	4062406106744
Item class	31A

**Description****Version:**

Tapered design.  
With Balluff/RFID chip bore.

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Extensions No. 301358, reducers No. 301359, coolant pipe No. 309880, socket for coolant pipe No. 309890.

**Note:**

Solid carbide arbors and extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

**Technical description**

Thread M	M8x25
Reach L <sub>1</sub>	25 mm
Overhang dimension A	51 mm
L <sub>2</sub>	5 mm
Bore Ø D <sub>1</sub>	8.5 mm
Ø D <sub>2</sub>	13 mm

External Ø D	15 mm
Adapter	HSK-A 63
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Type of product	Threaded copy mill arbor