

Garant**Arbor for screw-in milling cutters with thread tapered form, HSK-A 63, Thread M × Length L1: M12X25****Order data**

Order number	307044 M12X25
GTIN	4062406106829
Item class	31A

Description**Version:**

Tapered design.
With Balluff/RFID chip bore.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Extensions No. 301358, reducers No. 301359, coolant pipe No. 309880, socket for coolant pipe No. 309890.

Note:

Solid carbide arbors and extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

Technical description

Thread M	M12×25
Bore Ø D ₁	12.5 mm
Reach L ₁	25 mm
L ₂	5 mm
External Ø D	24 mm
Overhang dimension A	51 mm

Ø D ₂	21 mm
Adapter	HSK-A 63
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Type of product	Threaded copy mill arbor