

**Garant****Arbor for screw-in milling cutters with thread tapered form, HSK-A 63, Thread M × Length L1: M12X75****Order data**

Order number	307044 M12X75
GTIN	4062406106843
Item class	31A

**Description****Version:**

Tapered design.  
With Balluff/RFID chip bore.

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Extensions No. 301358, reducers No. 301359, coolant pipe No. 309880, socket for coolant pipe No. 309890.

**Note:**

Solid carbide arbors and extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

**Technical description**

Overhang dimension A	101 mm
Bore $\varnothing D_1$	12.5 mm
$\varnothing D_2$	21 mm
External $\varnothing D$	31 mm
$L_2$	5 mm
Thread M	M12×75

Reach L <sub>1</sub>	75 mm
Adapter	HSK-A 63
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Type of product	Threaded copy mill arbor