

**Garant****Arbor for screw-in milling cutters with thread tapered form, HSK-A 63, Thread M × Length L1: M16X150****Order data**

Order number	307044 M16X150
GTIN	4062406106911
Item class	31A

**Description****Version:**

Tapered design.  
With Balluff/RFID chip bore.

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Extensions No. 301358, reducers No. 301359, coolant pipe No. 309880, socket for coolant pipe No. 309890.

**Note:**

Solid carbide arbors and extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

**Technical description**

Thread M	M16×150
Ø D <sub>2</sub>	29 mm
Overhang dimension A	176 mm
L <sub>2</sub>	5 mm
Bore Ø D <sub>1</sub>	17 mm
External Ø D	42.5 mm

Reach L <sub>1</sub>	150 mm
Adapter	HSK-A 63
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Type of product	Threaded copy mill arbor