

**T-nut annealed, Slot width S: 16mm****Order data**

Order number	313805 16
GTIN	2050001929884
Item class	33T

**Description****Version:**

Precision ground, quenched, and tempered.

**Suitable for:**

Made by Röhms KFD-HE.

**Supplied with:**

Socket head screws DIN 912 - 12.9!

**Note:**

Other T-nuts available ex works.

**Technical description**

maximum tightening torque	70 Nm
suitable for Röhms KFD-HE	254
Bore spacing b	30 mm
Height H	21.5 mm
Thread G	M12

Step height h	8.5 mm
Slot width S	16 mm
Type of product	Tee-nut