

**T-nut annealed, Slot width S: 12mm****Order data**

Order number	313805 12
GTIN	2050001929860
Item class	33T

Description**Version:**

Precision ground, quenched, and tempered.

Suitable for:

Made by Röhms KFD-HE.

Supplied with:

Socket head screws DIN 912 - 12.9!

Note:

Other T-nuts available ex works.

Technical description

Height H	18.5 mm
Bore spacing b	20 mm
maximum tightening torque	50 Nm
suitable for Röhms KFD-HE	170
Thread G	M10

Step height h	7.5 mm
Slot width S	12 mm
Type of product	Tee-nut